





Mounting & Service Manual Go! Track

Philip Payne

MOUNTING




1 Base plate supplied with track adaptor.



2 Push a screwdriver into the slot provided to lever open the service hatch.



3 Insert the pictogram as shown in the picture above.





4 Put the battery connector in position. Push the battery wires downwards. Close the service hatch.





5 Mount the lightunit on the base plate.

WIRINGDIAGRAM



SPECTO XT (with GA69 track adaptor).




DALI (with GAC69 track adaptor).




TESTING

STATUS INDICATION:



ATS CYCLE:

Automatic
Test
System




SERVICE




1 Monthly and annual tests should be carried out in accordance with BS EN 50172:2004, 7.2. Clean the luminaire every year.



2 Remove the lightunit from the base plate by: (1) pushing both clickers on the side, (2) pulling the lightunit downwards.



3 Push a screwdriver into the slot provided to lever open the service hatch.



4 Change the battery if required autonomy isn't achieved. Remove the battery with a screwdriver. Write the installation date on the battery label of the new installed battery.



Go! Track

SPECIFICATION

| Type | Voltage | Power consumption* | Current | Power factor |
|-----------|--------------|--------------------|---------|--------------|
| DALI | 230V / 50 Hz | 2 W | 17 mA | 0,6 |
| SPECTO XT | 230V / 50 Hz | 2 W | 17 mA | 0,6 |

*maximum values at switched-on light source and not fully charged battery



| | |
|-------------------|--|
| Mounting | Installation on normal flammable surfaces. |
| Temperature range | +5 °C till +40 °C |
| Dimensions | See www.philippayne.co.uk |
| Autonomy | 3 hours |
| Light source | Led |
| ATS | Automatic Test System (IEC 62034) |
| Battery | 3,6V 1,1 Ah NiMH (AA cell) |
| Protection rate | IP40 (IP20 with track adaptor) |
| Insulation class | Class II, double insulated (no ground connection needed). |
| Material | Polycarbonate (PC) |

Warranty, accessories and spacing tables and further information see www.philippayne.co.uk